



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:  $\geq 1000M \Omega$
- Contact resistance:  $\leq 10m\Omega$
- After environmental testing :  $\leq 20m\Omega$

X2530 H XX- PT  
① ② ③ ④

- ① Series No.
- ② Category : H-HSG
- ③ Appearance type:Blank-Ordinary
- ④ Row No.-Pin No.: XX-02P~22P
- ⑤ Material : PT-PBT 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.54	5.60	7.10	12	27.94	31.00	32.50
03	5.08	8.14	9.64	13	30.48	33.54	35.04
04	7.62	10.68	12.18	14	33.02	36.08	37.58
05	10.16	13.22	14.72	15	35.56	38.62	40.12
06	12.70	15.76	17.26	16	38.10	41.16	42.66
07	15.24	18.30	19.80	17	40.64	43.70	45.20
08	17.78	20.84	22.34	18	43.18	46.24	47.74
09	20.32	23.38	24.88	19	45.72	48.78	50.28
10	22.86	25.92	27.42	20	48.26	51.32	52.82
11	25.40	28.46	29.96	22	53.34	56.40	57.90

X2530H-XX-PT	PBT UL 94V-0	X2530T	X2530W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X2530H-XX-N0
DWN	DATE	VIEW:	PART NO.: 2.5mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn