



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压:800V AC/分钟

Temperature range:-25°C~+85°C

温度范围: -25°C~+85°C

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X2530 H X-2xXX X-PT XX

① ②③ ④ ⑤⑥ ⑦

1.Series No

2.Category:H-HSG

3.Welding Board Angle:Blank-ordinary

4.Row No-Pin No:2xXX-2x02P~2x32P

5.Plug the Pin&Special No:

6.Materail:PT-PBT 94V-0

7.Color:Blank-natural color black

poles	Dimensions(mm)			poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.54	5.52	7.12	2x13	30.48	33.46	35.06	2x24	58.42	61.40	63.00
2x03	5.08	8.06	9.66	2x14	33.02	36.00	37.60	2x25	60.96	63.94	65.54
2x04	7.62	10.60	12.20	2x15	35.56	38.54	40.14	2x26	63.50	66.48	68.08
2x05	10.16	13.14	14.74	2x16	38.10	41.08	42.68	2x27	66.04	69.02	70.62
2x06	12.70	15.68	17.28	2x17	40.64	43.62	45.22	2x28	68.58	71.56	73.16
2x07	15.24	18.22	19.82	2x18	43.18	46.16	47.76	2x29	71.12	74.10	75.70
2x08	17.78	20.76	22.36	2x19	45.72	48.70	50.30	2x30	73.66	76.64	78.24
2x09	20.32	23.30	24.90	2x20	48.26	51.24	52.84	2x31	76.20	79.18	80.78
2x10	22.86	25.84	27.44	2x21	50.80	53.78	55.38	2x32	78.74	81.72	83.32
2x11	25.40	28.38	29.98	2x22	53.34	56.32	57.92				
2x12	27.94	30.92	32.52	2x23	55.88	58.86	60.46				

X2530H-2xXX-PT	PBT UL 94V-0	X2530T	X2530W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期									units: mm
效										tolerance:
ΔX										X.X ±0.2mm
ΔX										X.XX ±0.1mm
ΔX										X.XXX ±0.05mm
MARK	文件工程章	DESCRIPTION	DATE	REVISED	APPROVED					UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector	
DWN		DATE		VIEW:	PART NO.:	
CHKD		DATE		UNIT: mm/in	2.54mm Crimp Style Connectors	
APPD		DATE		SIZE: A4	DWG NO.:	
					X2530H-2xXX-PT	
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0