



SECTION A-A
SCALE 1:1



SECTION B-B
SCALE 1:1



SECTION C-C
SCALE 1:1

■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤20mΩ
- After environmental testing : ≤30mΩ

X2581 T M-P SN

① ② ③ ④ ⑤

- ① Series No.
- ② Category : T-Terminal
- ③ Shape:M-male
- ④ Material: P-Phosphor bronze ;
- ⑤ Plating Style: SN-Bright Tin Plating (70u")

X2530TM-PSN	Phosphor Bronze	AWG#22-26	1.55mm(Mix.)	Stamping Before Plating 30-50u" Ni70-120u" Sn	X2550H
PART NO	Material	Wire Range	Insulation O. D.	Finish	Used In XKB Housing

广东星坤科技股份有限公司

生效

ΔX		日期	
ΔX		日期	
MARK	DESCRIPTION	DATE	REVISED

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X2530TM-PSN
DWN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章