



**Specifications:**

规格:  
**Voltage rating:**250V AC/DC  
 额定电压: 250V AC/DC  
**Current rating:**3A AC/DC  
 额定电流: 3A AC/DC  
**Withstanding voltage:**800V AC/minute  
 耐受电压:800V AC/分钟  
**Temperature range:**-25°C~+85°C  
 温度范围: -25°C~+85°C  
**Insulation resistance:**≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
**Contact resistance:**≤10mΩ  
 接触电阻: ≤10mΩ  
**After environmental testing:**≤20mΩ  
 环境测试: ≤20兆欧

**X2530 WR X-2xXX X-PT SN XX**

① ②③④ ⑤ ⑥⑦ ⑧ ⑨

1. Series No
2. Category:W-wafer
3. Welding Board Angle:R-Right Angle 90°
4. Welding Way:Blank-DIP
5. Row No-Pin No:2xXX-2x02P~2x32P
6. Plug the Pin&Special No:
7. Materail:PT-PBT 94V-0
8. Planting Category:SN-Bright tin plating
9. Color:Blank-natural color black

poles	Dimensions(mm)		poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B		A	B
2x02	2.54	7.62	2x13	30.48	35.56	2x24	58.42	63.50
2x03	5.08	10.16	2x14	33.02	38.10	2x25	60.96	66.04
2x04	7.62	12.70	2x15	35.56	40.64	2x26	63.50	68.58
2x05	10.16	15.24	2x16	38.10	43.18	2x27	66.04	71.12
2x06	12.70	17.78	2x17	40.64	45.72	2x28	68.58	73.66
2x07	15.24	20.32	2x18	43.18	48.26	2x29	71.12	76.20
2x08	17.78	22.86	2x19	45.72	50.80	2x30	73.66	78.74
2x09	20.32	25.40	2x20	48.26	53.34	2x31	76.20	81.28
2x10	22.86	27.94	2x21	50.80	55.88	2x32	78.74	83.82
2x11	25.40	30.48	2x22	53.34	58.42			
2x12	27.94	33.02	2x23	55.88	60.96			

X2530WR-2xXX-PTS	PBT UL 94V-0	Brass	Tin-Plated	X2530H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.: X2530WR-2xXX-PTS
APPD	DATE	SIZE: A4	WEIGHT 1.0g
KKB INDUSTRIAL PRECISION CO., LIMITED			SHEET 1/1
			REVISION A0

广东星坤科技股份有限公司  
 Recommended PCB Layout  
 General Tolerance±0.05

生	日期	units: mm	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX		tolerance:				
ΔX		X.X				
ΔX		X.XX				
MARK		X.XXX				
文件工程章						
REVISIONS						
www.xk-dg.cn						
www.hellokxb.com						
www.hellokxb.cn						