

Specifications:

Voltage rating: 250V AC / DC

Current rating: 5A AC / DC





Withstanding voltage: 1000V AC/minute

Temperature range: -25°C~+85°C

Insulation resistance: ≥1000MΩ

Contact resistance: ≤10mΩ


After environmental testing: ≤20mΩ



C3030 H M-2*XX XX-N2 XX

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: H-HSG
- ③ Welding Board Angle: M-Male HSG
- ④ Row No.-Pin No.: 2*XX-2*01P~2*12P
- ⑤ Plug the Pin & special No.
- ⑥ Material: N2-PA66 94V-2
- ⑦ Color: Blank-Natural Color



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*01			2*07	18.00	21.85
2*02	3.00		2*08	21.00	24.85
2*03	6.00	9.85	2*09	24.00	27.85
2*04	9.00	12.85	2*10	27.00	30.85
2*05	12.00	15.85	2*11	30.00	33.85
2*06	15.00	18.85	2*12	33.00	36.85

C3030HM-2*XX-N2	Nylon 66 94V-2	C3030TF	C3030W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

ΔX 效

ΔX 日期

ΔX 文件工程章

MARK DESCRIPTION REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

DATE	REVISED	APPROVED	units:	mm
			tolerance:	
			X.X	±0.2mm
			X.XX	±0.1mm
			X.XXX	±0.05mm
				UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.: 3.00 mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	DWG NO.: C3030HM-2*XX-N2
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT · SHEET · REVISION 1.0g 1/1 A0