




Specifications:
 Voltage rating: 600V AC/ DC
 Current rating: 1A AC/DC
 Withstanding voltage: 1800V AC/minute
 Temperature range: -25° ~ +105°
 Insulation resistance: ≥1000MΩ
 Contact resistance: ≤20mΩ
 After environmental testing: ≤40mΩ

X4001 W V-02 L-LP SN
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category: W-WAFER
- ③ Welding Board Angle: V-180°
- ④ Row No.-Pin No.: 02P
- ⑤ Plug the Pin & Special No.: L-With Lock
- ⑥ Material: LP-LCP 94V-0
- ⑦ Plating Category: SN-Bright Tin Plating



X4001WV-02L-LP SN	LCP UL 94V-0	Phosphor Bronze	Tin-Plated	Brass	Tin-Plated
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tab)	Finish (Solder Tab)

广东星坤科技股份有限公司

生 日期
 日期
 ΔX
 MARK
 文件工程章

REVISIONS	DATE	REVISED	APPROVED	DESCRIPTION
				UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A
DWN	DATE	VIEW:
CHKD	DATE	UNIT: mm/in
APPD	DATE	SIZE: A4
KKB INDUSTRIAL PRECISION CO., LIMITED		

MODEL TYPE: X4001WV-02L-LP SN
PART NO.: 4.00mm BTB Style Connectors
DWG NO.:
WEIGHT 1.0g
SHEET 1/1
REVISION A0