



Specifications:
 Voltage rating:30V AC/DC
 Current rating:0.5 A AC/DC
 Withstanding voltage: 500V AC/minute
 Temperature range:-40° ~+55
 Insulation resistance:≥100MΩ



	MATERIAL	PLATING
terminal 1	Brass	AG
terminal 2	Phosphor Bronze	AG
terminal 3	Phosphor Bronze	AG
plastic	PA66	
Axle sleeve	Brass	Au

					ANGULAR	±5°	DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5 PHONE JACK				
Δx					L ≤ 4	±0.2	DWN		DATE		VIEW:	PART NO.:				
Δx					4 < L ≤ 16	±0.3	CHKD		DATE		UNIT: mm/in	DWG NO.:				
Δx					16 < L ≤ 63	±0.4	APPD		DATE		SIZE: A4	PJ-210				
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5						WEIGHT	SHEET	REVISION		
REVISIONS					UNSPECIFIED TOLERANCES		KXB INDUSTRIAL PRECISION CO., LIMITED					1.0g	1/1	A0		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																