




PJ-3135-



PJ-3136-


SCHMATIC



R:red	G:green
Y:yellow	B:black
W:white	I:transparent

SPECIFICATION

1. Rating: DC 30V 10A
2. Contact resistance:  $\leq 30m\Omega$
3. Insulation resistance:  $\geq 100m\Omega$
4. Withstand voltage: 500VAC
5. Insertion and extraction force: 3-20N
6. life test: 5,000 cycles



Ø3.5 MATING PLUG

	MATERIAL	PLATING
terminal 2	Phosphor Bronze	tin
terminal 3	Phosphor Bronze	tin
terminal 4	Phosphor Bronze	tin
plastic	Pbt	

广东星坤科技股份有限公司

生效日期

文件工程章

日期

REVISIONS

www.helloxkb.com www.helloxkb.com www.helloxkb.com

DSND	DATE	SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: PJ-313X-X
APPD	DATE	SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED			1.0g 1/1 A0

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	