



G: Gold plated
S: Silver plated



SPECIFICATION

1. Rating: DC 30V 0.5A;
2. Contact resistance: $\leq 50\text{m}\Omega$;
3. Insulation resistance: $\geq 100\text{m}\Omega$ (DC250V)
4. Withstand voltage: 500VAC;
5. Insertion and extraction force: 3-25N;
6. Life test: 5,000 cycles.

SCHEMATIC



	MATERIAL	PLATING
terminal 2	Phosphor Bronze	tin
terminal 3	Phosphor Bronze	tin
terminal 4	Phosphor Bronze	tin
plastic	Pbt	

广东星坤科技股份有限公司

生效日期

文件工程章

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.: PJ-376X-X
APPD		DATE		SIZE: A4	
UNSPECIFIED TOLERANCES					WEIGHT
XKB INDUSTRIAL PRECISION CO., LIMITED					SHEET
					REVISION
					1.0g
					1/1
					A0