



- 1.RATING: DC 30V 0.5A;
- 2.Contact resistance: $\leq 0.03\Omega$;
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V);
- 4.Withstand voltage: 500v ac;
- 5.Insertion and extraction force: 3-20n;
- 6.Life test: 5,000 cycles min



| | MATERIAL | PLATING |
|------------|-----------------|---------|
| terminal 1 | Phosphor Bronze | tin |
| terminal 2 | Phosphor Bronze | tin |
| terminal 3 | Brass | tin |
| terminal 4 | Brass | tin |
| terminal 5 | Phosphor Bronze | tin |
| plastic | Pbt | |

广东星坤科技股份有限公司

生效日期

文件工程章

日期

REVISIONS

www.helloxkb.com www.helloxkb.com www.helloxkb.com

| | | | | | |
|------------------------|--|------|--|--------------------------------------|-------------------------------|
| DSND | | DATE | | SCALE: N/A | MODEL TYPE: 3.5 PHONE JACK |
| DWN | | DATE | | VIEW: | PART NO.: |
| CHKD | | DATE | | UNIT: mm/in | DWG NO.: PJ-324MX |
| APPD | | DATE | | SIZE: A4 | |
| UNSPECIFIED TOLERANCES | | | | XKB INDUSTRIAL PRECISION CO.,LIMITED | WEIGHT 1.0g |
| | | | | | SHEET 1/1 |
| | | | | | REVISION A0 |