




| Code-x | H | Code-x | H |
|--------|------|--------|------|
| A | 4.3 | O | 11.0 |
| B | 4.5 | P | 11.5 |
| C | 5.0 | Q | 12 |
| D | 5.5 | R | 12.5 |
| E | 6.0 | S | 13.0 |
| F | 6.5 | T | 13.5 |
| G | 7.0 | U | 14.0 |
| H | 7.5 | V | 15.0 |
| I | 8.0 | W | 15.5 |
| J | 8.5 | X | 16 |
| K | 9.0 | Y | 16.5 |
| L | 9.5 | Z | 17 |
| M | 10.0 | | |
| N | 10.5 | | |

SPECIFICATION

Contact rating: 50mA, 12V DC
 Contact Resistance: 100mΩ max
 Dielectric Strength: 250V AC/1minute
 Travel: 0.25mm
 Operating Temp: -30°C ~ +85°C
 Storage Temp: -30°C ~ +80°C



| | |
|-----------------|-------------------------|
| PAPT NO | TC-1102DE-X-X |
| Operating Force | A:100gf B:160gf C:260gf |
| Height | Code-x |



| ⑤ | Terminal | 3 | Brass (0.30t) | ag Plated | | |
|------|-----------|--------|---------------|------------|-----------|--------|
| ④ | Contact | 1 | F ag/SUS | | | |
| ③ | Base | 1 | PPA | | | |
| ② | Cover | 1 | Brass | Tin plated | | |
| ① | Keystake | 1 | PPA | | | |
| ITEM | PAPT NAMF | TER,NO | QTY | MATERIAL | FINISHING | REMARK |

广东星坤科技股份有限公司

| | |
|----|----|
| 生效 | 日期 |
| 文件 | 工程 |
| 印章 | |

| | |
|------------|------------------------|
| units: | mm |
| tolerance: | X.X ±0.2mm |
| | X.XX ±0.1mm |
| | X.XXX ±0.05mm |
| | UNSPECIFIED TOLERANCES |

| | | | | | | | |
|---------------------------------------|--|------|--|-------------|---------------|-------|----------|
| DSND | | DATE | | SCALE: N/A | MODEL TYPE: | | |
| DWN | | DATE | | VIEW: | TACT SWITCH | | |
| CHKD | | DATE | | UNIT: mm/in | PART NO.: | | |
| APPD | | DATE | | SIZE: A4 | DWG NO.: | | |
| XKB INDUSTRIAL PRECISION CO., LIMITED | | | | | TC-1102DE-X-X | | |
| | | | | | WEIGHT | SHEET | REVISION |
| | | | | | 1.0g | 1/1 | A0 |