




SPECIFICATION

Contact Rating: 50mA, 12V DC
 Contact Resistance: 100mΩ max
 Insulation Resistance: 100mΩ min, 500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 0.25mm
 Operating Temp: -20°C~+70°C
 Storage Temp: -30°C~+80°C



A:With B:without

PAPT NO	TS-1101S-X-X-A-X-X
Operating Force	A:100gf B:160gf C:260gf
Height	H:A:4.3 B:5.0 C:6.0 D:7.0
Fixed column	A:With B:without
Color	B:black W:white
Pin pitch	P



P	L	L1
A	8.0	10

⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—	
④	Contact	—	1	F.ag/Sus	Natural	—	
③	Base	—	1	Lcp	—	—	
②	Cover	—	1	Spcc	Plating Nickel	—	
①	Keystake	—	1	Pa46	—	—	
ITEM	PAPT	NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

广东星坤科技股份有限公司

生效日期

文件工程章

REVISIONS	UNSPECIFIED TOLERANCES		
DESCRIPTION	DATE	REVISED	APPROVED
DATE	REVISED	APPROVED	

DSND	DATE	SCALE: N/A	MODEL TYPE: TACT SWITCH
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: TS-1101S-X-X-A-X-X
APPD	DATE	SIZE: A4	WEIGHT: 1.0g
XKB INDUSTRIAL PRECISION CO., LIMITED			SHEET: 1/1
			REVISION: A0

www.helloxb.com www.helloxb.cn