



CIRCUITDIAGRAM



SPECIFICATION

Contact Rating: 50mA, 12V DC  
 Contact Resistance: 100mΩ max  
 Insulation Resistance: 100mΩ min. 500V DC  
 Dielectric Strength: 250V AC/1minute  
 Travel: 0.25mm  
 Operating Temp: -30℃~+85℃  
 Storage Temp: -30℃~+80℃

PCB LAND DIMENSION



PAPT NO	TS-1159B-X-X-X
Operating Force	A:100gf B:160gf C:260gf D:320gf E:400gf
Height	H: A:3.4 B:4.2 C:4.8 D:5.1
Color	BL:blue W:white

⑤	Terminal	—	4	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	PA46		—
②	Cover	—	1	SPSS	Plating Nickel	—
①	Keystake	—	1	Silica gel		—
ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

广东星坤科技股份有限公司  
 生效 [ ] 日期 [ ]  
 文件工程章

ΔX								
ΔX								
ΔX								
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A
	REVISIONS					DWN	DATE <td>VIEW: </td>	VIEW:
						CHKD	DATE <td>UNIT: mm/in</td>	UNIT: mm/in
						APPD	DATE <td>SIZE: A4</td>	SIZE: A4

MODEL TYPE: TACT SWITCH		
PART NO.:		
DWG NO.: TS-1159B-X-X-X		
WEIGHT	SHEET	REVISION
1.0g	1/1	A0

XKB INDUSTRIAL PRECISION CO., LIMITED