


IP67

SPECIFICATION


Contact Rating: 50mA,12V DC
 Contact Resistance: 100mΩ max
 Insulation Resistance: 100mΩ min.500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 0.25mm
 Operating Temp: -30°C~+85°C
 Storage Temp: -30°C~+80°C

PAPT NO	TS-1159UB-X-X-X
Operating Force	A:100gf B:160gf C:260gf D:320gf E:400gf
Height	H:A:3.5 B:4.3 C:4.9 D:5.2
color	W:white BL:blue

CIRCUIT DIAGRAM



PCB LAYOUT MOUNTING PATTERN



ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	4	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Pa46		—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	Silica gel		—

					units: mm	DSND	DATE	SCALE: N/A	MODEL TYPE: TACT SWITCH
					tolerance: X.X ±0.2mm	DWN	DATE	VIEW:	PART NO.:
					X.XX ±0.1mm	CHKD	DATE	UNIT: mm/in	DWG NO.:
					X.XXX ±0.05mm	APPD	DATE	SIZE: A4	TS-1159UB-X-X-X
REVISIONS					UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT SHEET REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn									1.0g 1/1 A0