




**SPECIFICATION**

Contact Rating: 50mA, 12V DC  
 Contact Resistance: 100mΩ max  
 Insulation Resistance: 100mΩ min. 500V DC  
 Dielectric Strength: 250V AC/1minute  
 Travel: 0.25mm  
 Operating Temp: -30°C ~ +85°C  
 Storage Temp: -30°C ~ +80°C



PCB LAYOUT PLAN



CIRCUIT DIAGRAM

PAPT NO	TS-CB1157-X-X
Operating Force	A:100gf B:160gf C:260gf
Height	H:A:3.8 B:4.3

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	5	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	PA46		—
②	Cover	—	1	Brass	Plating Nickel	—
①	Keystake	—	1	PA46		—

广东星坤科技股份有限公司

生	日期
ΔX	
ΔX	
ΔX	
MARK	

DSND		DATE		SCALE: N/A	MODEL TYPE: TACT SWITCH
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.:
APPD		DATE		SIZE: A4	TS-CB1157-X-X
UNSPECIFIED TOLERANCES				XKB INDUSTRIAL PRECISION CO., LIMITED	WEIGHT 1.0g
					SHEET 1/1
					REVISION A0

文件工程章

REVISIONS  
 www.helloxkb.com www.helloxkb.cn