


P.C.B LAYOUT

TOP VIEW



	MATERIAL	PLATING
center pin	copper	nickel
terminal 1	brass	tin
terminal 2	copper alloy	tin
terminal 3	brass	tin
plastic	PBT	

SCHEMATIC	
Model	DC-012B-2.5A
Center Pin	Ø2.0 mm
Center Pin	Ø2.5 mm

广东星坤科技股份有限公司

生效日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ*					ANGULAR ±5° L ≤ 4 ±0.2 4 < L ≤ 16 ±0.3 16 < L ≤ 63 ±0.4 L > 63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: DC POWER JACK
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: DC-012B-2.5A-2.0
APPD	DATE	SIZE: A4	WEIGHT SHEET REVISION 1.0g 1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED