




PCB LAYOUT



SCHEMATIC

NOTE:
 Rating: DC 12V 50mA
 Operating Force:200±100gf
 Lifetime:10,000 Cycles



PAPT NO	L
SK-1500-L1	1.5
SK-1500-L2	2.0
SK-1500-L3	2.5

5	Terminal	—	6	Brass (0.30t)	ag Plated
4	Contact spring	—	1	Phosphor bronze	ag Plated
3	Base	—	1	Lcp	Black
2	Cover	—	1	Sus	Natural
1	Keystake	—	1	Pa46	Black
ITEM	PAPT NAME	TER.NO	QTY	MATERIAL	FINISHING

广东星坤科技股份有限公司

生	日期
ΔX	日期
ΔX	
ΔX	
MARK	

文件工程章

DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

units: mm
 tolerance:
 X.X ±0.2mm
 X.XX ±0.1mm
 X.XXX ±0.05mm

DSND	DATE	SCALE: N/A
DWN	DATE	VIEW:
CHKD	DATE	UNIT: mm/in
APPD	DATE	SIZE: A4

MODEL TYPE:	WEIGHT	SHEET	REVISION
SLIDE SWITCH	1.0g	1/1	A0
PART NO.:			
DWG NO.:			

KKB INDUSTRIAL PRECISION CO., LIMITED

SK-1500-X