


NOTE:  
Operating Force:  
lever portion 70 ± 40gf  
Push portion 200 ± 40gf



Circuit Diagram

P.C.B Mounting  
Pattern Dimension

| ITEM | PART NAME | TER.NO | QTY | MATERIAL   | FINISHING      | REMARK |
|------|-----------|--------|-----|------------|----------------|--------|
| ⑥    | Terminal  | —      | 8   | Brass      | Plating silver | —      |
| ⑤    | Contact   | —      | 1   | F.ag/Brass | Plating silver | —      |
| ④    | Base      | —      | 1   | Pa46       | —              | —      |
| ③    | Spring    | —      | 1   | Sus        | Natural        | —      |
| ②    | Cover     | —      | 1   | Sus        | Natural        | —      |
| ①    | Keystake  | —      | 1   | Pa46       | —              | —      |

广东星坤科技股份有限公司

生效 日期  
文件印章

|                                       |      |      |                |  |
|---------------------------------------|------|------|----------------|--|
| DSND                                  | 日期   | DATE | SCALE: N/A     | MODEL TYPE:<br>MULTI-FUNCTIONAL SWITCH |
| DWN                                   | 文件印章 | DATE | VIEW:          | PART NO.:                              |
| CHKD                                  | 文件印章 | DATE | UNIT: mm/in    | DWG NO.:                               |
| APPD                                  | 文件印章 | DATE | SIZE: A4       | TM-1011A                               |
| XKB INDUSTRIAL PRECISION CO., LIMITED |      |      | WEIGHT<br>1.0g | SHEET<br>1/1                           |
| UNSPECIFIED TOLERANCES                |      |      | REVISION<br>A0 |  |

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | ANGLAR      | ±5°  |
|------|-------------|------|---------|----------|-------------|------|
| ΔX   |             |      |         |          | L ≤ 4       | ±0.2 |
| ΔX   |             |      |         |          | 4 < L ≤ 16  | ±0.3 |
| ΔX   |             |      |         |          | 16 < L ≤ 63 | ±0.4 |
| MARK |             |      |         |          | L > 63      | ±0.5 |