






FREE



PUSH



FEATURES

- 特征
- Light operating force.
- 轻操作力。
- Long term low contact resistance.
- 长期接触电阻低。
- Mom entary or latching operation.
- 固定或闭锁操作。
- Short stroke 2.0mm to latch.
- 短行程2.0毫米至闭锁。
- Compact spacing on PCB of 8.5mm.
- PCB上的紧凑间距为8.5mm。

SPECIFICATIONS

1.ELECTRICAL

Contact rating	0.1A,30VDC
Contact resistance	50mWMax.
Insulation resistance	100MWMIn. at 250VDC
Dielectric strength	250VAC Min. for 60 sec.

2.MECHANICAL AND ENVIRONMENTAL

Temperature rating	Operating:-15 to+55 Storage: -25 °C to +65 °C
Operation force	160±80gf
Stroke	Lock Stroke: 2.0±0.2mm Full Stroke: 2.5±0.2mm
Operating life	full load: 1x10 <sup>6</sup> cycles no load: 1 x10 <sup>7</sup> cycles
Contact form	DPDT

PAPT NO	XKB8585-X-170
OPERATION	W:NO LOCK Z:LOCK

⑦	Contact	— 2	Phosphor bronze	Plating silvering	—	
⑥	Terminal	— 6	Brass	Plating silvering	—	
⑤	Spring	— 1	Sus	Natural	—	
④	Base	— 1	Pbt	—	—	
③	Crochet Needle	— 1	Sus	Natural	—	
②	Cover	— 1	Pom	—	—	
①	Keystake	— 1	Pom	—	—	
ITEM	PAPT NAMF	TERNO	QTY	MATERIAL	FINISHING	REMARK

广东星坤科技股份有限公司

生	日期		
效			
Δ			
Δ			
MARK	DESCRIPTION		
文件	工程章		
REVISIONS	DATE	REVISED	APPROVED
UNSPECIFIED TOLERANCES			

DSND	DATE	SCALE: N/A	MODEL TYPE: KEY SWITCH
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: XKB8585-X-170
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0