



- NOTE:
1. Rating: DC 5V 10mA
 2. Contact Resistance: 100mΩMAX
 3. Insulation Resistance: 100mΩMIN
 4. Soldering Temper: 260±5°/5s
 5. Mechanical Life: 100,000 cycles
 6. Ever Portion 80±50gf
 7. Push Portion 205±80gf
 8. Travel: -24° 0° +24°

A向24°a与b
 B向24°a与d
 C向150g
 a与c通

ITEM	PAPT NAMF	TER.NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	5	Phosphor Bronze	Plating silver		
④	Base	1	Lcp			
③	Spring	1	Sus	Natural		
②	Cover	1	Sus	Natural		
①	Keystake	1	Ppa			

广东星坤科技股份有限公司

生 效 日期

文件工程章

REVISIONS

UNSPECIFIED TOLERANCES

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: MULTI-FUNCTIONAL SWITCH		
						DWN	DATE	VIEW:	PART NO.:		
						CHKD	DATE	UNIT: mm/in	DWG NO.:		
						APPD	DATE	SIZE: A4	TM-2011		
						XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g	SHEET: 1/1	REVISION: A0