



Circuit Diagram

ITEM	PAPT	NAMF	TER.NO	QTY	MATERIAL	FINISHING	REMARK
⑥	Terminal	---	5	Brass(0.15t)	Plating silver	---	---
⑤	Contact	---	1	F.ag/Brass	Plating silver	---	---
④	Base	---	1	Lcp	---	---	---
③	Spring	---	1	Sus	Natural	---	---
②	Cover	---	1	Sus	Natural	---	---
①	Keystake	---	1	Pa46	---	---	---

NOTE:
 Operating Force
 lever portion 80 ± 50 gf
 Push portion 205 ± 50 gf

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: MULTI-FUNCTIONAL SWITCH
Δx					ANGLAR ±5°	DWN	DATE	VIEW:	PART NO.:
Δx					L ≤ 4 ±0.2	CHKD	DATE	UNIT: mm/in	DWG NO.:
Δx					4 < L ≤ 16 ±0.3	APPD	DATE	SIZE: A4	TM-2022-X
Δx					16 < L ≤ 63 ±0.4				WEIGHT
Δx					L > 63 ±0.5				SHEET
									1.0g
									1/1
									A0