






- 1.RATING:DC 12V,50mA Max
- 2.TRAVEL:0.15±0.05mm
- 3.LIFE:300,000cycles
- 4.PACKAGE:5000Pcs/Reel



PAPT NO	TS-2630A-X
Operating Force	B:200gf C:260gf
Height	H:0.45



Recommended PAD Layout  
Recommended solder thickness T=0.1±0.01



CIRCUIT DIAGRAM

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	4	Brass (0.30t)	AG Plated	—
④	Contact	—	2	F.ag/Sus		—
③	Base	—	1	LCP		—
②	Cover	—	1	Kapton	Tin plated	—
①	Keystake	—	1	PET		—

REVISIONS					UNSPECIFIED TOLERANCES			DSND	DATE	SCALE: N/A	MODEL TYPE:		
ΔX					units: mm			DWN	DATE	VIEW:	TACT SWITCH		
ΔX					tolerance: X.X ±0.2mm			CHKD	DATE	UNIT: mm/in	PART NO.:		
ΔX					X.XX ±0.1mm			APPD	DATE	SIZE: A4	DWG NO.:		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm						TS-2630A-X		
								XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											1.0g	1/1	A0