



■ Specifications :

- Voltage rating: 100V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ

X2016 W V-XX K- N0 SN

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : V-Stright 180°
- ④ Row No.-Pin No.: XX-02P~20P
- ⑤ Plug the Pin & Special No.:K-Kink;K1-Reverse Kink;
- ⑥ Material : N0-PA66 94V-0
- ⑦ Plating Category: Sn-Bright Tin Plating;V01-Gold Flash

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	4.80	12	22.00	26.00	24.80
03	4.00	8.00	6.80	13	24.00	28.00	26.80
04	6.00	10.00	8.80	14	26.00	30.00	28.80
05	8.00	12.00	10.80	15	28.00	32.00	30.80
06	10.00	14.00	12.80	16	30.00	34.00	32.80
07	12.00	16.00	14.80	17	32.00	36.00	34.80
08	14.00	18.00	16.80	18	34.00	38.00	36.80
09	16.00	20.00	18.80	19	36.00	40.00	38.80
10	18.00	22.00	20.80	20	38.00	42.00	40.80
11	20.00	24.00	22.80				

X2016WW-XXK-N0V01	Nylon 66 UL 94V-0	Brass	Gold-Flash	X2016H
X2016WW-XXK-N0SN		Tin-Plated		
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X2016WW-XXK-N0SN
DWN	DATE	VIEW:	PART NO.: 2.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn