


Specification


MATERIAL:
 Insulator: LCP UL94V-0, BLACK
 Contact: C5210
 SHELL: SUS304

PLATING:
 Contact: G/F OVER Ni
 Shell: G/F PLATED ON SOLDER AREANI
 PLATED OVERALL

Electrical:
 Current Rating :0.5mA AC/DC max.
 Voltage Rating :125V AC/DC
 Ambient Temperature Range :-20C~+60°C
 Storage Temperature Range: -40C~+70°C
 Ambient Humidity Range :95% R.H. Max.
 Contact Resistance: 100mΩ max.
 Insulation Resistance 1000MΩ min./500VDC
 Mating Cycles: 10,000 Insertions
 Reflow peak temp: 260°C +50, 3-5 5
 Mating Cycles: 3,000 Insertions Min



SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出



广东星坤科技股份有限公司

生	日期
效	日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
					ANGLAR ±5°
					L ≤ 4 ±0.2
					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: SIM CARD CONN
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: XKSIM-304
APPD	DATE	SIZE: A4	WEIGHT 1.0g
XKB INDUSTRIAL PRECISION CO., LIMITED			SHEET 1/1
			REVISION A0