



- Specifications :**
- Voltage rating: 250V AC / DC
  - Current rating: 5A AC / DC
  - Withstanding voltage: 1000V AC/minute
  - Temperature range: -25°C~+85°C
  - Insulation resistance: ≥1000M Ω
  - Contact resistance: ≤10m Ω
  - After environmental testing : ≤20mΩ

X3025 WRS-2\*XXD-LP-XX-XX

- Series No.
- Category: W-WAFER
- Welding Board Angle: R-Straight ht 18°
- Welding Way: S-SMT
- Row No.-Pin No.: 2\*XX-2\*02P-2\*22P
- Plug the Pin & Special No.: D-With Solder Tabs
- Material: LP-LCP 94V-0
- Plating Category: SN-Bright Tin Plating; G05-Contact Gold 5u" SW-Fog Tin plating
- Color : Blank-Natural Color

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*01	6.65	---	2*07	24.65	18.00
2*02	9.65	3.00	2*08	27.65	21.00
2*03	12.65	6.00	2*09	30.65	24.00
2*04	15.65	9.00	2*10	33.65	27.00
2*05	18.65	12.00	2*11	36.65	30.00
2*06	21.65	15.00	2*12	39.65	33.00

X3025 WRS-2*XXD-LPSW	LCP UL 94V-0	Brass	Matte Tin	Brass	Tin-Plated	X3025H
X3025 WRS-2*XXD-LPG05			Ni 5u/Min or 13u/Min Contact Area Gold 5u/Min.			
X3025 WRS-2*XXD-LPSN			Tin-Plated			
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tab)	Finish (Solder Tab)	Mates With XKB Housing

广东星坤科技股份有限公司

生	日期
發	
Δ	
文件工程章	

REVISIONS  
www.heloxkb.com

				XKB	ANGULAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5
UNSPECIFIED TOLERANCES						

DSND	DATE	SCALE: NA	MODEL TYPE:
DWNN	DATE	VIEW:	X3025WRS-2*XXD-XXXX
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	3.00 mm Crimp Style Connectors
			DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT
			1.0g
			SHEET
			1/1
			REVISION
			A0