



■ Specifications :

- Voltage rating: 30 V AC / DC
- Current rating: 0.5A AC / DC
- Withstanding voltage: 200V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:  $\geq 100M\Omega$
- Contact resistance:  $\leq 20m\Omega$
- After environmental testing:  $\leq 40m\Omega$

X0800 H-XX -46 HF

- ① Series No.
- ② Category : H-HSG
- ③ Row No. Pin No. XX-02P~20P
- ④ Material: 46-PA46 94V-0
- ⑤ HF-Halogen Free

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	0.80	1.80	4.40	12	8.80	9.80	12.40
03	1.60	2.60	5.20	13	9.60	10.6	13.2
04	2.40	3.40	6.00	14	10.4	11.4	14.0
05	3.20	4.20	6.80	15	11.2	12.2	14.8
06	4.00	5.00	7.60	16	12.0	13.0	15.6
07	4.80	5.80	8.40	17	12.8	13.8	16.4
08	5.60	6.60	9.20	18	13.6	14.6	17.2
09	6.40	7.40	10.0	19	14.4	15.4	18.0
10	7.20	8.20	10.8	20	15.2	16.2	18.8
11	8.00	9.00	11.6				

X0800H-XX-46HF	PA46 UL 94V-0 Halogen Free	X0800T	X0800W
PART NO	Material(Wafer)	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X0800H-XX-46HF
DWN	DATE	VIEW:	PART NO.: 0.8mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn