




SECTION: B-B



SECTION: A-A



Specifications:

规格:

Voltage rating: 30V AC/DC
 额定电压: 30V AC/DC
 Current rating: 0.5A AC/DC
 额定电流: 0.5A AC/DC
 Withstanding voltage: 200V AC/minute
 耐压电压: 200V AC/分钟
 Temperature range: -25°C ~ +85°C
 温度范围: -25°C ~ +85°C
 Insulation resistance: ≥100MΩ
 绝缘电阻: ≥100MΩ
 Contact resistance: ≤20mΩ
 接触电阻: ≤20mΩ
 After environment testing: ≤40mΩ
 环境试验后: ≤40mΩ

X0800 T-P XX X

① ② ③ ④

- ① Series Number
- ② Category: T-terminal
- ③ Material: P-Phosper bronze
- ⑦ SN-Bright Ni: 30-50u " SN: 70-120U"
- V01 -All Gold Flash

X0800T-PSN	High conductive Brass	AWG# 32-36	0.39mm (Max)	Phosphor Bronze	Tin-Plated	X0800W
X0800T-PV01						
PART NO	Material	Wire Range	Insulation O.D.	Material (Terminal)	Finish (Terminal)	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期
發	
Δ	
文件工程章	

REVISIONS

NO.	DATE	REVISED	APPROVED

UNSPECIFIED TOLERANCES

www.xkkg.cn www.helloxkb.com www.hellioxkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE: X1259HV-XX-No
DWNN	DATE	VIEW:	PART NO.: 0.80mm IDC Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0