

Specifications:

规格:

Voltage rating: 30V AC/DC

额定电压: 30V AC/DC

Current rating: 0.5A AC/DC

额定电流: 0.5A AC/DC

Withstanding voltage: 200V AC/minute

耐压电压: 200V AC/分钟

Temperature range: -25°C ~ +85°C

温度范围: -25°C ~ +85°C

Insulation resistance: ≥100MΩ

绝缘电阻: ≥100MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

After environment testing: ≤40mΩ

环境试验后: ≤40mΩ

X0800 T-P XX X

① ② ③ ④


① Series Number

② Category: T-terminal


③ Material: P-Phosphor bronze

⑦ SN-Brignt Ni: 30-50u " SN: 70-120u" V01 -All


Gold Flash



SECTION-B-B



SECTION-A-A



X0800T-PSN	High conductive Brass	AWG #32-36	0.38mm (Max)	Phosphor Bronze	Tin-Plated	X0800V
X0800T-PV01						
PART NO	Material	Wire Range	Insulation O.D	Material (Terminal)	Finish (Terminal)	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

www.xkpcb.com www.hellixkb.com

ANGLR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X1259HV-XX-N0
DWVN	DATE	VIEW:	PART NO.: 0.80mm IDC Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g SHEET: 1/1 REVISION: A0