



■ Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤40mΩ

X1002 W V S- XX-B XX- XX XX
 ① ② ③ ④ ⑤ ⑥

- Series No.
- Category : W-WAFER
- Wedding Board Angle : V-Stright Angle 180°
- Welding Way:S-SMT
- Row No.Pin No.XX-02P~20P
- Plug the Pin & Special No:B-Ultra-thin With Lock HF-Halgen Free
- Material:6T-PA6T;1T-PA10T;HT-HTN 6T 94V-0
- Planting Category:
 SN-Bright tin plating 70u" Min.;30" Ni Min.
 SW-Matte Tin plating 70u" Min.;30u" Ni Min

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.00	3.70	2.50	12	11.00	13.70	12.50
03	2.00	4.70	3.50	13	12.00	14.70	13.50
04	3.00	5.70	4.50	14	13.00	15.70	14.50
05	4.00	6.70	5.50	15	14.00	16.70	15.50
06	5.00	7.70	6.50	16	15.00	17.70	16.50
07	6.00	8.70	7.50	17	16.00	18.70	17.50
08	7.00	9.70	8.50	18	17.00	19.70	18.50
09	8.00	10.70	9.50	19	18.00	20.70	19.50
10	9.00	11.70	10.50	20	19.00	21.70	20.50
11	10.00	12.70	11.50				

X1002WWS-XXBHf-6TSW	PA6T UL 94V-0 (Halogen Free)	Phorphos Bronze	Matte Tin Plating
X1002WWS-XXB-1TSW	PA10T UL 94V-0		
X1002WWS-XXB-HTSW	HTN6T UL 94V-0		
X1002WWS-XXB-6TSW	PA6T UL 94V-0		
X1002WWS-XXB-6TSN	PA6T UL 64V-0		
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)

广东星坤科技股份有限公司
 Recommended P.C.B Layout
 General Tolerance±0.05

生效
 ΔX
 ΔX
 ΔX
 MARK

日期

DESCRIPTION

REVISIONS

DATE REVISED APPROVED UNSPECIFIED TOLERANCES

ANGLAR ±5°
 L ≤ 4 ±0.2
 4 < L ≤ 16 ±0.3
 16 < L ≤ 63 ±0.4
 L > 63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: X1002WWS-XXB-6TSN
DWN	DATE	VIEW:	PART NO.: 1.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn