



Specification

Insulator Material: Polysetr, UL94V-0

Standard: P A6T

Contact Material: Brass

Contact plated: Gold Over Nickel

Poles: 2*7P (Double)

Current Rating : 3Amp

Contact Resistance: 20 Milliohms Max

Insulation Resistance : 1000MΩ Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40 °C -- +105 °C

核准:		日期:		品名规格: 210R-2*7P 三翘 弯排针 PA6T料 客户料号 C2902695 单位 mm 比例 / 版本 A	
业务:		日期:			
制图:		日期:		深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD	
SXA		2019-11-01			
未注公差表					
X.X	±0.2				
X.XX	±0.10				
X.XXX	±0.050				
图纸编号:		B-2100R14P-E010		版本 A	