



**Specification**

Insulator Material: Polyseter, UL94V-0

Standard: PA6T

Contact Material: Brass

Contact plated: Gold Over Nickel

Poles: 2~40P

Current Rating : 3Amp

Insulation Resistance : 1000MΩ Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40℃ -- +105℃

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:				
CHECKED:	DATE:	<b>深圳市灿科盟实业有限公司</b> CHANKEMENG INDUSTRY CO., LTD			
DRAWN:	DATE:	<b>TITLE:</b> 210S-1*8P 双翅 L=11.6mm (3.6/5.0/3.0)			
YAN	2011-08-24	CLIENT P/N	C2902693	UNIT	mm
		FILE NO.	B-2100S08P-C000	SCALE	Free
				REV.	A