



RECOMMENDED PCB LAYOUT  
COMPONENT SIDE VIEW

**SPECIFICATION**

Current Rate:3Amp  
 Contact Resistance:20mΩ MAX at DC 1A  
 Insulation Resistance:1000MΩ MIN.atDC500V  
 Dielectric Strength:AC500V PER minute  
 Operation Temperature:-40°to +105°

**MATERIAL**

Insulator:Polyester ,UL94V-0  
 Standard:PA6T  
 CONTACT: Phosphor Bronze  
 Contact plated: Gold Over Nickel  
 Color:Black

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	深圳市灿科盟实业有限公司 KIMT W CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 220S-2*4P H=5.0 封闭式 (U型)			
DRAWN:	DATE:	CLIENT P/N	C2902687	UNIT	mm
Juli-Liu	2016-08-26	SCALE	Free	REV.	A
		FILE NO.	B-2200S08P-B420		