



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material:Housing:Nylon66, UL94V-0

编 号	尺寸 (mm)	
	A	B
HC-PHD-2*2Y	2.00	6.00
HC-PHD-2*3Y	4.00	8.00
HC-PHD-2*4Y	6.00	10.00
HC-PHD-2*5Y	8.00	12.00
HC-PHD-2*6Y	10.00	14.00
HC-PHD-2*7Y	12.00	16.00
HC-PHD-2*8Y	14.00	18.00
HC-PHD-2*9Y	16.00	20.00
HC-PHD-2*10Y	18.00	22.00
HC-PHD-2*11Y	20.00	24.00
HC-PHD-2*12Y	22.00	26.00
HC-PHD-2*13Y	24.00	28.00
HC-PHD-2*14Y	26.00	30.00
HC-PHD-2*15Y	28.00	32.00
HC-PHD-2*16Y	30.00	34.00
HC-PHD-2*17Y	32.00	36.00
HC-PHD-2*18Y	34.00	38.00
HC-PHD-2*19Y	36.00	40.00
HC-PHD-2*20Y	38.00	42.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生	料号 PART NO.	A2004-2XNY	版本 REV.	A		
			X.±0.25	X.*±2'		2013、07、01		品名 TITLE		PHD孔座	页次 SHEET	1/1
			.X±0.20	.X*±1'		张名		客户料号 CUTL. NO.				
			.XX±0.15	.XX*±0.5'		2013、07、03		张名				
.XXX±0.10	.XXX*±0.5'	核准 APPROVAL	2013、07、05	单位 UNITS	MM	比例 SCALE	1:1	深圳市华灿天禄电子有限公司				