


Circuit Diagram



| NO.1     |     |
|----------|-----|
| PART NO. | H   |
| A        | 1.5 |
| D        | 2.0 |

| NO.3    |              |
|---------|--------------|
| PART NO | MATERIAL/QTY |
| S       | SUS/1PC      |
| D       | SUS/2PCS     |

| NO.2    |         |
|---------|---------|
| PART NO | vigor   |
| 1       | 70±30   |
| 2       | 100±50  |
| 3       | 160±50  |
| 4       | 260±50  |
| 5       | 320±80  |
| 6       | 350±80  |
| 7       | 520±130 |

| NO.4    |               |
|---------|---------------|
| PART NO | NOTE          |
| 1~9     | SERIAL NUMBER |

| NO.5    |           |
|---------|-----------|
| PART NO | NOTE      |
| B       | Bulk      |
| R       | Tape&Reel |

| ITEM | PART NAME  | QTY. | MATERIAL        | FINISHING      |
|------|------------|------|-----------------|----------------|
| ⑥    | Dust Cover | 1    | Kapton Film     | Yellow         |
| ⑤    | Terminal   | 4    | Phosphor Bronze | Plating silver |
| ④    | Contact    | 1    | F.Ag/SUS        | Natural        |
| ③    | Base       | 1    | Nylon           | Black          |
| ②    | Cover      | 1    | SPCC            | Natural        |
| ①    | Keystoke   | 1    | Nylon           | White          |

|                |          |           |                    |            |
|----------------|----------|-----------|--------------------|------------|
| APPROVALS      |          | DATE      | DRAWING NO.        |            |
| DRAWN          | G.M.Chen | 2015/6/17 | TD-115.3SG-XXN-XXX |            |
| CHECKED        |          |           | TACT SWITCHES      |            |
| APPROVALS      |          |           | TITLE:             |            |
| TOLERANCES ARE |          | 30~0.1±   | ±0.30              | ANGLE      |
|                |          | 10~0.10   | ±0.20              | UNIT: mm   |
|                |          | 5~0.10    | ±0.10              | SCALE: 1:1 |
| ECN NO.        | REV.     | DATE.     | DESCRIPTION.       | PROJ.      |
|                | A        |           | NEW                |            |
|                |          |           |                    |            |
|                |          |           |                    |            |

