



PCB HOLES(TOP VIEW)
GENERAL TOLERANCE:0.1mm

Temperature -20~70 C
 Rated Load DC 30V 0.5A
 Contact Resistance <0.03Ω
 Insulation Resistance >100MΩ
 Withstand Voltage AC500V(50Hz)/min
 Actuating Force 3~30N
 Life 5000 Cycles

	MATERIAL	PLATING
terminal 2	Phosphor Bronze	cusn
terminal 3	Phosphor Bronze	snsb
terminal 4	Phosphor Bronze	snsb
terminal 5	BRASS	cusn
terminal 6	BRASS	cusn
plastic	PBT	

Model No.	PJ-3582-	PJ-3583-
Schematic		
color	B:Black W:White	

广东星坤科技股份有限公司

生效日期

文件工程章

REVISIONS

www.helloxkb.com www.helloxkb.com www.helloxkb.com

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	3.5 PHONE JACK
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.: PJ-358X-X
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT SHEET REVISION
			1.0g 1/1 A0

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES