

NOTES1:

- UL Standard
- Rated voltage/current : 300V / 8A
- Withstanding voltage : AC1600V/1Min.

IEC Standard

1. Pollution degree	2	2	3
Overvoltage category	II	III	III
Rate impulse voltage(KV)	2.5KV	2.5KV	2.5KV
Rate voltage(V)	320V	250V	160V
Rate current(A)	7A		

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 3.81mm, Poles : N=02~24P
- 3.Operating temperature: -40°C~+105°C
- 4.Undimensioned tolerances:





Pitch range in mm		Nominal dimension range in mm		Tolerance	
Over	Under	Over	Under	Over	Under
6	10	30	60	100	150
TO	TO	TO	TO	TO	TO
10	24	30	60	100	150
				±2°	
±0.15		±0.30		±0.50	
				±0.70	
				±1.00	
				±1.30	

5.RoHS Compliance

Ordering Information

JL15EDGA-381 XX G 0 1

- Pitch 381=3.81PH
- No.of pins 2P,3P,4P~24P
- Housing Color G=Black G=Green B=Blue V=White Y=Yellow D=Drange E=Grey
- Packing Q=Fe 80g U=Tube A=Tray



2	Clamp	Copper alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

JILN 东莞市锦凌电子有限公司
DONGGUAN JINLING ELECTRONIC CO., LTD

DRAW	SHUANGPING ZHENG
CHECK	LICHAD LIU
APPROVE	YONGLIANG GAO

SCALE	FIT	PART NO.	TITLE:
UNIT	mm		
SIZE	A4	JL15EDGA-381XXG01	JL15EDGA-381-XXP 插拔式母座/弯脚/绿色
SHEET	1/1		
PRD			

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW		21.04.13