








ROHS



- NOTE:
- 1.Rating:DC30V 0.1A
 - 2.OP:10.70±0.8
 - 3.Operating froce:30±15gf
 - 4.Mechanical Life:3,000,000

⑦	Lever	—	1	Stainless Steel	—	—
⑥	Shrapnel	—	1	Beryllium Copper	—	—
⑤	Contact	—	1	Ag	—	—
④	Terminal	—	3	Brass(0.52t)	Plating silver	—
③	Housing	—	1	PBT	White	—
②	Knob	—	1	PBT	White	—
①	Cover	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 ELECTRONICS CO.,LTD		
DRAWN	JKUN.LU		2015.4.21				
CHECKED			TITLE:				MICRO SWITCHES
APPROVALS			PART NO.				K9-1267U-H11.8
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm	
			10~30	±0.20			
			5~10	±0.15			
			~ 5	±0.10			
			±2'		DRAWING NO.	SCALE: 1:1	
					PROJECT	SHEET 1 OF 1	

ECN NO.	REV.	DATE.	NEW	CHANGE.	CHECK.	APPRO.
	A					
DESCRIPTION.						