

## **SPECIFICATIONS**

#### **Mechanical**

Plug Mating Force: 3.00kg (6.61Lb) max. Plug Unmating Force: 0.40~3.00kg (0.88~6.61Lb) Contact Retention Force: 0.50kg (1.10Lb) min. Durability: 1500 Cycles


## Electrical

Current Rating: 1.00A Contact Resistance: 50mΩ max(Initial) 100 mΩ max(After life test) Dielectric Withstanding Voltage: 500V AC/1min min. Insulation Resistance: 100MΩ min.

#### Physical


Housing: Thermoplastic, UL 94V-0 rated Contact: Copper alloy Plating: See "ORDERING INFORMATION" Operating Temperature: -25 to +85 Recommended Thickness of PCB: 1.60[.063]


## DRAWING



## ORDERING INFORMATION

## PRODUCT NO.: JA 3 3 3 3 1 - HA1P-4 F





# Audio Jack Connector

JA Series Triple HD Jack, R/A, T/H Type 3.5mm [.138"] 13 Pos.

