

**HSF** RoHS us CE

**SPECIFICATIONS**

Rated(额定参数): 125V,4A  
 Dielectric strength(抗电强度): AC1250V/1 Minute  
 Insulation Resistance(绝缘电阻):1000MΩ Min  
 Contact Resistance(接触电阻):20mΩ Max  
 Wire Range(线径):20~28AWG  
 Strip length(剥线长度):8mm  
 Temp. range(操作温度): -40℃~+105℃  
 MAX Soldering(瞬时温度):+250℃,5s

Housing Material(塑件): PA66 (UL94 V-0)  
 Contact(端子): Phosphor Bronze, Tin plating(磷铜镀锡)

PITCH RANGE IN MM			NOMINAL DIMENSION RANGE IN MM				
T0	OVER 6	OVER 10	T0	OVER 30	OVER 60	OVER 100	OVER 150
6	T0 10	T0 24	30	T0 60	T0 100	T0 150	
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70	±1.00

**Ordering Information**





**JL15EDGKD - 250 XX X X 1**

Pitch  
250=2.50PH

No.of pins  
2P,3P,4P~24P

Housing Color  
B=Black  
G=Green  
U=Blue  
R=Red  
W=White  
Y=Yellow  
O=Orange  
E=Grey

Packing  
O=Pe bag  
T=Tube  
A=Tray



OPERATION		DRAW	yiyusheng	20.05.22	SCALE	FIT
X.X	±0.30					
X.XX	±0.20	CHECK			UNIT	mm
X.XXX	±0.10				SIZE	A4
Angle	±3°	APPROVE			SHEET	1/1
DIM	TOL				PROJ.	

**JILN** 深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992

A0

2020.05.22 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION CHANGE

PART NO. JL15EDGKD-250XXXX1

TITLE: 2.50 Pitch Female Pluggable Terminal Blocks