



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 适用线规: AWG#30~#22.
4. 额定电压: 250V DC/AC (rms).
5. 额定电流: 3.0A.
6. 接触电阻: $\leq 20\text{m}\Omega$.
7. 耐压值: 1000V AC/minute.
8. 绝缘电阻: $\geq 1000\text{M}\Omega$.

Poles	Dimensions (mm)	
	A	B
2	2.50	7.50
3	5.00	10.00
4	10.00	12.50
5	10.00	15.00
6	12.50	17.50
7	15.00	20.00
8	17.50	22.50
9	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
13	30.00	35.00
14	32.50	37.50
15	35.00	40.00
16	37.50	42.50

APPROVALS		DATE	TITLE:		PART NO.	SCALE:	SHEET
DRAWN	G.M.Chen	2015/7/17	CONNECTOR		XH-□□□A	1:1	1 OF 1
CHECKED			ELECTRONICS CO.,LTD				
APPROVALS							
TOLEFRANCES ARE	30 ^{±0.15}	±0.30	ANGLE	±2°	DRAWING NO.		PROJ.
	10 ^{±0.10}	±0.20					
	5 ^{±0.10}	±0.15					

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			