


P.C.B. LAYOUT SCALE 8:1



CIRCUIT DIAGRAM



GT-TC094X-HXXX-LX

G-SWITCH

Operating Force
A=160gf

Switch Height (mm)
H023=2.3mm

Switch lifetime (Force)
L1=100,000 Cycles

G-Switch Specification:

Operating temperature range -30 to +85
 Rating 50mA.12V DC
 Insulation resistance: 100MΩ min.100V DC
 Dielectric strength 250V AC for 1 min
 Contact resistance: 100m Ω max.
 Travel:0.25±0.1mm



G-Switch Electronic (HongKong) CO.,Ltd.

Unless otherwise specified, Tolerance:
 X. ±0.30
 X.x ±0.20
 X.xx ±0.15
 X.xxx ±0.10
 Angles ±3°

DESIGN FengFengChen DATE 2019.05.29
 CHECKED DATE
 APPROVED DATE
<http://www.dg-switch.com>
 TEL:0769-82388879

Molde code:
GT-TC094X-HXXX-LX
 REV.: X1 SCALE: 4:1 UNIT: mm
 SIZE: A4 SHEET: 1/1