

SPECIFICATIONS

Rated (额定参数) : 300V, 8A
 Dielectric strength (抗电强度) : AC2000V/1 Minute
 Insulation Resistance (绝缘电阻) : 1000MΩ Min
 Contact Resistance (接触电阻) : 20mΩ Max
 Wire Range (线径) : 28~12AWG
 Strip length (剥线长度) : 5-8mm
 Temp. range (操作温度) : -40°C~+105°C
 MAX Soldering (瞬时温度) : +250°C, 5s






Housing Material (塑件) : PA66 (UL94 V-0)
 Contact(端子): Brass, Tin plating(黄铜镀锡)
 Clamp(方块): Brass(黄铜), Ni plating(镀镍)
 Screw (螺丝): M2.0, Steel, Tin plating(钢, 镀镍)

	PITCH RANGE		NOMINAL DIMENSION RANGE				
	IN	MM	OVER	OVER	OVER	OVER	OVER
T0	6	10	TO	30	60	100	OVER
6	10	24	TO	30	70	100	150
	±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70 ±1.00

Ordering Information

JL15EDGKR-381 XX G 01

Pitch 381-3, 81
 No. of pins 2P-24P
 Housing Color
 B=Black
 G=Green
 U=Blue
 R=Red
 W=White
 Y=Yellow
 O=Orange
 E=Grey
 Packing
 0=Pe bag
 A=Tray
 T=Tube



DRAW	SHUANG PING ZHENG		SCALE	FIT	PART NO.	TITLE:
	CHECK	LICHAO LIU	UNIT	mm		
APPROVE	YONGLIANG GAO		SIZE	A4	JL15EDGKR-381XXG01	JL15EDGKR-3.81-XXP插拔式母座/绿色
			SHEET	1/1		
			PROJ.			

JILIN 东莞市锦凌电子有限公司
 DONGGUAN JINLING ELECTRONIC CO., LTD

JL15EDGKR-381XXG01

JL15EDGKR-3.81-XXP插拔式母座/绿色