





Specification:

1. Rating: 6A 120VAC
2. Contact resistance: $\leq 30 \text{ m}\Omega$
3. Insulation resistance: $\geq 100 \text{ M}\Omega$ (DC500V/Min)
4. Electronics life: > 10000 cycles
5. Operation force: $250 \pm 100 \text{ gf}$



SS-12M11 X X



广东星坤科技股份有限公司

生	日期
效	日期
文件	工程
MARK	章

units:	mm
tolerance:	
X.X	$\pm 0.2 \text{ mm}$
X.XX	$\pm 0.1 \text{ mm}$
X.XXX	$\pm 0.05 \text{ mm}$
UNSPECIFIED TOLERANCES	

DSND	DATE	SCALE: N/A
DWN	DATE	VIEW:
CHKD	DATE	UNIT: mm/in
APPD	DATE	SIZE: A4
XKB INDUSTRIAL PRECISION CO., LIMITED		

MODEL TYPE:	SLIDE SWITCH	
PART NO.:		
DWG NO.:	SS-12M11XX	
WEIGHT	SHEET	REVISION
1.0g	1/1	A0