



PCB Layout(Pattern Side)

△

NO.1	
PART NO.	H
A	3.8
B	4.3
C	4.8
D	5
E	5.5
F	6
G	6.5
H	7
I	7.5
J	8
K	8.5
L	9
M	10

NO.2	
PART NO.	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.3	
PART NO.	MATERIAL/qty
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
F	C5210/2PCS

NO.4	
PART NO.	L
A	6.5
B	7.0
	8.0

NO.5-NO.6	
PART NO.	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	4	Brass(0.30)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	PA46	Black	—
②	Cover	—	1	SUS	—	—
①	Keystroke	—	1	PA46	Black	—

APPROVALS		DATE	
DRAWN	J.X.Zhong	2013/6/24	
CHECKED		TITLE: TACT SWITCHS	
APPROVALS		PART NO. K2-1109SP-□□□□-□□	
TOLERANCES ARE		SCALE: 1:1	
30~12.5	±0.30	ANGLE	PROJ.
10~30	±0.20	UNIT: mm	
5~10	±0.15	DRAWING NO.	
~5	±0.10		

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	B		△ NEW			
	A					



ELECTRONICS CO.,LTD

TACT SWITCHS

PART NO. K2-1109SP-□□□□-□□

SCALE: 1:1

PROJ.

SHEET 1 OF 1