



环保物料

TEL: 0769-82001899





SPECIFICATIONS

- 1.Voltage rating: 125V AC, DC
  - 2.Current rating: 1A, AC, DC
  - 3.Withstanding Voltage: 250V AC/minute
  - 4.Insulation resistance:100M min
  - 5.Temperature range: -25 °C-+85 °C
  - 6.Contact resistance: 20m max
- WAFER  
 Housing Material: PA9T UL 94V0  
 Pin Material: Phosphor Bronze or Brass  
 Contact Area Plating: Plated Tin or Plated Gold  
 Mates with :P1258 series Housing  
 Poles:02-30P



P.C.B. LAYOUT



Unit: mm

PART NO.	Dimensions		
	A	B	C
02P	1.25	7.65	7.60
03P	2.50	8.90	8.85
04P	3.75	10.15	10.10
05P	5.00	11.40	11.35
06P	6.25	12.65	12.60
07P	7.50	13.90	13.85
08P	8.75	15.15	15.10
09P	10.00	16.40	16.35
10P	11.25	17.65	17.55
11P	12.50	18.90	18.85
12P	13.75	20.15	20.10
13P	15.00	21.40	21.35
14P	16.25	22.65	22.60
15P	17.50	23.90	23.85
16P	18.75	25.15	25.10
20P	23.75	30.15	30.10
30P	36.25	42.65	42.60

				TOLERANCE UNLESS OTHERWISE	DRAWN	CK tan	<b>XFCN</b> 兴飞连接器有限公司 XFCN CONNECTORS CO.,LTD.	SHEET	1/1	
				X. ±0.30 X° ±5°	CHKD			DATE	2020.04.12	
				.X ±0.20 .X° ±2°	APPD			UNITS	mm	
				.XX ±0.08 .XX° ±1°	VIEW	⊕		SCALE	1:1	
AO	MODIFICATION	DRAW	DATE	.XXX ±0.03 .XXX° ±0.5°			PRODUCT NAME	1.25mm Crimp Style Connectors	DWG NO.	009
1	2	3	4	5	6	7	PART. NO.	M1258RS-xxP	8	9
10										