


Kinghelm®

REVISIONS				
REV NUMBER	DESCRIPTION	DWN	CHK	DATE
A	DESIGN			



NOTES:

- 1. ELECTRICAL:**
- 1.1. VOLTAGE RATING:DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPENS/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- 2. MATERIAL:**
- 2.1. SEE TABLE
- 3. ALL COMPONENTS ARE ROHS COMPLIANT.**

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿I-PEX, 1.13端子, 镀金	1
②	接头	SMA母头母针, 带4个脚, 11牙, 镀金	1
①	同轴线	RF1.13黑线, OD:1.13mm	AS

深圳市金航标电子有限公司 WWW.BDS666.COM

KH-IPEXA-SMAKWE-B080H 0755-83044319

ALL DIMENSION ARE IN MM		DRAWN		DATE
CHKD.	James	James	2021-10-30	
APPD.	Frank	Frank	2021-10-30	
COMPUTER GENERATED IN SOLIDWORKS		Scott	2021-10-30	

I-PEX 1.13 TO SMA /F L=80mm

DO NOT SCALE THIS DRAWING		GENERAL TOLERANCE FOR ANGLES	
± 1° ±	0.5	0.25	0.150

PROJECTION	SCALE	Free	TYPE	SHEET	1	OF
	B	K	XXX	A		

CUSTOMER P/N:

4

3

2

1

A

B

C

D

A

B

C

D