



PART NO.	L	Operating force
MS-12D19-G2	2	200±100gf
MS-12D19-G3	3	
MS-12D19-G4	4	

⑤	Contact Spring	2	Beryllium copper	Ag Plated
④	Terminal	3	Brass Strip	Ag Plated
③	Base	1	NYLON	Black
②	Cover	1	SUS	Natural
①	Knob	1	NYLON	Black
ITEM	PART NAME	QTY.	MATERIAL	FINISHING

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2014/8/18	MS-12D19-G	
CHECKED			TITLE: SLIDE SWITCHES	
APPROVALS			PART NO. MS-12D19-G	
TOLERANCES ARE		30 <sup>±0.15</sup>	±0.30	ANGLE
		10 <sup>±0.10</sup>	±0.20	UNIT: mm
		5 <sup>±0.10</sup>	±0.15	SCALE: 1:1
				SHEET 1 OF 1
				PROJ.

ECN NO.	REV.	DATE.	DESCRIPTION.
	A		NEW

