			A	В		С		D		E		F		G
2		5.00 <u>0191140</u> ,15			12.00[0.472]		320001388			() 3	Circuit d	liagram 2 }\ 4		1
							PCB	Layout	[2007]					
3										SPECIFICATIONS CONTACT RATING:AC/DC 42V,100mA MECHANICAL LIFE:100000 cycles CONTACT RESISTANCE:100mΩmax.(initial) INSULATION RESISTANCE:1000MΩ min.100VDC DIELECTRIC STRENGTH:250VAC/1 min OPERATING TEMPERATURE:-40°C to +80°C Button gram force:970gf				
	A4							UNIT	MM	PROJCTED	$\oplus \square$	PRODUCT		
	A3					COMMON T	OLERANCE	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:		
5	A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN		www.rocpu.	tw 5
	A1				ROCPU	X.X X	± 0.15 ± 0.25	ROC	<b>PU</b>	TECHN		ONGY		TD
	REV	DATE				ANGULAR Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus witho							without permission	
		A B C D E F G												ف