		A	В	C	D		E		F	G	
2	4.50(0.177)±0.15		8.40[0.331]	03.50(0.138				( ()- (3-		am ② ④	2
3					3 Layout	4.50(0.177)	CONT/ MECH/ CONT/ INSUL/ DIELE OPER/	ANICAL   ACT RES ATION R CTRIC S	ING:AC/DC 42 LIFE:1000000 SISTANCE:100 ESISTANCE:1 TRENGTH:250 EMPERATURI	cycles )mΩ max。(in 000MΩ min.10	0VDC
A	4			COMMON TOLERANCE	UNIT	MM	PROJCTED	⊕⊅	PRODUCT N	AME:	
5 A				X.XX ± 0.10	DRAWN BY DATE	FUYUAN 2019	CHECKED BY APPROVAL B		MODEL NO:		5
			ROCPU	X.XX ± 0.10   X.X ± 0.15	ļ I					www.rocpu.tw	
R		REVISION DESCRIPTION	ISSUE	X ± 0.25			TECHN				
		A	B	C	D	ici coniidence ar	nd shall not be reproduced or o E		F	G	