



NOTE :  
 Rating 额定功率: DC 12V 50mA  
 Operating Force 操作力: 200±100gf  
 Lifetime 寿命: 10,000 Cycles

ITEM	PAPT NAME	TER.NO	QTY	MATERIAL	FINISHING	REMARK
5	Terminal	---	8	Brass (0.30t)	ag Plated	---
4	Contact spring	---	1	Phosphor branze	ag Plated	---
3	Base	---	1	Lcp	Black	---
2	Cover	---	1	Sus	Natural	---
1	Keystake	---	1	Pa46	Black	---

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	

UNIT	MM	PROJECTED	
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL	B ALEN

PRODUCT NAME:  
 MODEL NO: TP-1401L2  
 Https: www.rocpcu.tw

**ROCPCU TECHNOLOGY CO.,LTD**

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission